

No: 21195-249

BiClamp[®] E LAP forceps



Dimensions and weight

Shaft diameter	5 mm
Length	340 mm
Cable length	with connecting cable 4 m

Basic features

Shape / Forming	fenestrated
Connection	{MF-2-Stecker}

Surface

Branches	smooth
Coating	with non-adhesive coating

Cleaning and Reprocessing

Cleaning in washer disinfectant	max 95 °C
Sterilization in autoclave	max 138 °C

Additional product information

Packaging unit	1 Piece
Max. electrical capacity	0.25 kVp